

# ZS2001-0010 | female header with push-in termination as plug-in connection level, black, 2 x 5 pin, 3.5 mm grid size, packaging unit = 5



Printed circuit board connector, female, 10-pin



Electrical data	
Rated voltage	160 V
Rated current	8 A
Mechanical data	
Connector type	Printed circuit board connector
Contact type	female
Number of positions (face)	10-pin
Wire termination	Push-in
Way of locking	screw
Weight per piece	5,898 g (0.0130 lb)
Body color	black
Contact plating	Tin
Max. wire cross-section	AWG16 (1.5 mm <sup>2</sup> )
Environmental data	
RoHS compliant	yes
Protection rating	IP20

## Dimensions

## Notes

- Illustrations similar

## Ordering information

ZS2001-0010

female header with push-in termination as plug-in connection level, IP20, black, for ELM72xx modules, slot X1 Digital IO, 2 x 5 pin



Products marked with a crossed-out wheeled bin shall not be discarded with the normal waste stream. The device is considered as waste electrical and electronic equipment. The national regulations for the disposal of waste electrical and electronic equipment must be observed.

Beckhoff®, TwinCAT®, TwinCAT/BSD®, TC/BSD®, EtherCAT®, EtherCAT G®, EtherCAT G10®, EtherCAT P®, Safety over EtherCAT®, TwinSAFE®, XFC®, XTS® and XPlanar® are registered trademarks of and licensed by Beckhoff Automation GmbH. Other designations used in this publication may be trademarks whose use by third parties for their own purposes could violate the rights of the owners.

© Beckhoff Automation GmbH & Co. KG 09/2023

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual application do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.