



# ZS7000-C022 | B40 crimp contact, female, 10 mm<sup>2</sup>

## B40, female



Mechanical data	
Accessories type	Crimp contact
Installation size	B40
Contact type	female
Wire termination	crimp connection
Mating cycles	≥ 100
Contact plating	Ni, Au gal.
Contact material	copper alloy
Max. wire cross-section	10.0 mm <sup>2</sup>
Stripping length	10 mm + 0,5 mm
Contact diameter	4.5 mm

## Notes

- Illustrations similar

## Ordering information

ZS7000-C022

B40 crimp contact, female, 10 mm<sup>2</sup>, packaging unit = 25 pieces

Products marked with a crossed-out wheeled bin shall not be discarded with the normal waste stream. The device is considered as waste electrical and electronic equipment. The national regulations for the disposal of waste electrical and electronic equipment must be observed.

Beckhoff®, TwinCAT®, TwinCAT/BSD®, TC/BSD®, EtherCAT®, EtherCAT G®, EtherCAT G10®, EtherCAT P®, Safety over EtherCAT®, TwinSAFE®, XFC®, XTS® and XPlanar® are registered trademarks of and licensed by Beckhoff Automation GmbH. Other designations used in this publication may be trademarks whose use by third parties for their own purposes could violate the rights of the owners.

© Beckhoff Automation GmbH & Co. KG 03/2023

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual application do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.