



ZK1091-1001-0xxx | Fiber-optic cables for EK1501, EK1521, CU1521, CU1521-0010 (multimode 50/125 μm)



SC connector multimode, plug, straight – SC connector multimode, plug, straight



Plugs

Electrical data	Head A	Head B
Mechanical data		
Installation size	SC connector multimode	SC connector multimode
Connector type	plug	plug
Configuration	straight	straight
Wire termination	crimp connection	crimp connection
Way of locking	push-pull	push-pull
Body color	gray	gray
Max. cable outer diameter	0.9 ... 3.0 mm	0.9 ... 3.0 mm
Environmental data		
RoHS compliant	yes	yes
Ambient temperature (operation)	-40...+85°C, -40...+185°F	-40...+85°C, -40...+185°F

Cable

Electrical data	
Mechanical data	
Cross-section	2 x AWG10
Outer cable diameter	3,7 mm x 6,2 mm
Min. bending radius, moved	15 x outer cable diameter
Min. bending radius, fixed installation	9 x outer cable diameter
Use	drag-chain suitable
Wall thickness of wire insulation	0,5 mm
Wall thickness of jacket	0,6 mm
Jacket color	orange
Wire color code	green, green
Printing color	black
Max. tensile load, dynamic	600 N
Environmental data	
Operation temperature range, fixed installation	-5...+70°C, 23...+ 158°F
Ambient temperature, transport/storage	-25...+70°C, -13...+158°F
Flame-retardant	according to IEC 60332-1 and IEC 60332-3
Halogen-free	according to IEC 60754-2
UL	yes, UL 1651 OFNR

Dimensions	

Notes

- The following length tolerances apply: 2-3%
- Illustrations similar

Ordering information	Length
ZK1091-1001-0001	1.00 m
ZK1091-1001-0005	5.00 m
ZK1091-1001-0010	10.00 m
ZK1091-1001-0015	15.00 m
ZK1091-1001-0020	20.00 m

ZK1091-1001-0025	25.00 m
ZK1091-1001-0045	45.00 m
ZK1091-1001-0050	50.00 m
ZK1091-1001-0055	55.00 m
ZK1091-1001-0070	70.00 m
ZK1091-1001-0110	110 m
ZK1091-1001-0115	115 m
ZK1091-1001-0125	125 m
ZK1091-1001-0160	160 m
ZK1091-1001-0175	175 m
ZK1091-1001-0180	180 m
ZK1091-1001-0220	220 m
ZK1091-1001-0230	230 m
ZK1091-1001-0300	300 m
ZK1091-1001-0345	345 m
ZK1091-1001-0600	600 m



Products marked with a crossed-out wheeled bin shall not be discarded with the normal waste stream. The device is considered as waste electrical and electronic equipment. The national regulations for the disposal of waste electrical and electronic equipment must be observed.

Beckhoff®, TwinCAT®, TwinCAT/BSD®, TC/BSD®, EtherCAT®, EtherCAT G®, EtherCAT G10®, EtherCAT P®, Safety over EtherCAT®, TwinSAFE®, XFC®, XTS® and XPlanar® are registered trademarks of and licensed by Beckhoff Automation GmbH. Other designations used in this publication may be trademarks whose use by third parties for their own purposes could violate the rights of the owners.

© Beckhoff Automation GmbH & Co. KG 02/2024

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual application do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.