


ZK2000-2121-3xxx | Sensor cable, PVC, 3 x 0.25 mm², fixed installation



M8, plug, straight, male, 3-pin, A-coded – M8, plug, straight, male, 3-pin, A-coded



Plugs

Electrical data	Head A	Head B
Rated voltage	60 V (according to IEC 61076-2-104)	60 V (according to IEC 61076-2-104)
Rated current (signal/24V)	4 A at 40 °C (acc.to IEC 61076-2-104)	4 A at 40 °C (acc.to IEC 61076-2-104)
Shielding	no	no
Insulation resistance	≥ 10 GΩ (according to IEC 60512-2)	≥ 10 GΩ (according to IEC 60512-2)
Mechanical data		
Installation size	M8	M8
Connector type	plug	plug
Configuration	straight	straight
Contact type	male	male
Number of positions (face)	3-pin	3-pin
Coding	A-coded	A-coded
Wire termination	crimp connection	crimp connection
Recommended torque, nut	0.4 Nm	0.4 Nm


Mating cycles	≥ 100 (according to IEC 60512-9a)	≥ 100 (according to IEC 60512-9a)
Way of locking	screw	screw
Weight per piece	0.028 kg (0.0617 lb)	0.028 kg (0.0617 lb)
Body color	black	black
Body material	TPU, UL94	TPU, UL94
Coupling nut material	CuZn, Ni	CuZn, Ni
Seal	FPM	FPM
Contact carrier color	red	red
Contact carrier material	TPU GF, UL 94	TPU GF, UL 94
Contact plating	Ni, Au gal.	Ni, Au gal.
Contact material	CuZn	CuZn
Environmental data		
Special features	halogen-free, flame-resistant as per IEC 60332-1-2, oil-resistant as per DIN EN 60811-2-1	halogen-free, flame-resistant as per IEC 60332-1-2, oil-resistant as per DIN EN 60811-2-1
RoHS compliant	yes	yes
Ambient temperature (operation)	-30...+80 °C, -22...+176 °F	-30...+80 °C, -22...+176 °F
Protection rating	IP67 in screwed condition (according to IEC 60529)	IP67 in screwed condition (according to IEC 60529)
Pollution level	3/2 (according to IEC 60664-1)	3/2 (according to IEC 60664-1)

Cable


Electrical data		
Rated voltage	≤ 300 V	
Insulation resistance	≥ 10 GΩ (according to IEC 60512-2)	
Wire resistance (signal/24V)	≤ 58.0 Ω/km (20 °C)	
Test voltage	≥ 3000 V	
Mechanical data		
Conductor construction (signal/24V)	32 x 0.10 mm	
Cross-section	3 x 0.25 mm ² (AWG24)	
Min. bending radius, fixed installation	10 x outer cable diameter	
Weight	29.45 kg/km (19.7 lb/1000 ft)	
Outer cable diameter	4.4 mm ± 0.15 mm (0.173" ± 0.0059")	
Shielding	no	
Use	fixed installation	
Jacket color	gray	
Material jacket	PVC (polyvinyl chloride)	

Wire color code	brown, blue, black
Wire insulation material	PVC (polyvinyl chloride)
Printing color	white
Environmental data	
Operation temperature range, fixed installation	-25...+80 °C, -13...+176 °F
Flame-retardant	according to DIN EN 60332-2-2
Halogen-free	no

Contact assembly



Dimensions



A1	39.60 mm
B1	39.60 mm

Notes

- Depending on the cable length (L), the following length tolerances apply:
0 m...<0.2 m: ± 10 mm | 0.2...4.0 m: + 40 mm | ≥ 4.0 m: + 1 %
- Illustrations similar
- Further cable length on request.

CE, UL

CE	yes
----	-----

Ordering information

Length

ZK2000-2121-3003	0.30 m
------------------	--------

Accessories

ZB8801-0000	torque wrench for hexagonal plugs, adjustable
-------------	---

ZB8801-0001	torque cable key, M8/wrench size 9, for ZB8801-0000
-------------	---



Beckhoff®, TwinCAT®, TwinCAT/BSD®, TC/BSD®, EtherCAT®, EtherCAT G®, EtherCAT G10®, EtherCAT P®, Safety over EtherCAT®, TwinSAFE®, XFC®, XTS® and XPlanar® are registered trademarks of and licensed by Beckhoff Automation GmbH. Other designations used in this publication may be trademarks whose use by third parties for their own purposes could violate the rights of the owners.

© Beckhoff Automation GmbH & Co. KG 07/2022

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual application do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.