

ZK1096-8181-0xxx | Industrial Ethernet/EtherCAT G/G10 cable, Cat.6/Cat.6A, PUR, 4 x 2 x AWG26, fixed installation



M12, plug, straight, male, 8-pin, X-coded – M12, plug, straight, male, 8-pin, X-coded



Plugs

Electrical data	Head A	Head B
Rated voltage	50 V AC / 60 V DC (according to IEC 61076-2-104)	50 V AC / 60 V DC (according to IEC 61076-2-104)
Rated current	0.5 A at 40°C	0.5 A at 40°C
Shielding	yes	yes
Contact resistance	< 5 mΩ	< 5 mΩ
Insulation resistance	≥ 100 MΩ	≥ 100 MΩ
Transmission characteristics	Cat.6A	Cat.6A
Mechanical data		
Installation size	M12	M12
Connector type	plug	plug
Configuration	straight	straight
Contact type	male	male

Number of positions (face)	8-pin	8-pin
Coding	X-coded	X-coded
Recommended torque, nut	0.6 Nm	0.6 Nm
Mating cycles	≥ 100 (according to IEC 60512-9a)	≥ 100 (according to IEC 60512-9a)
Way of locking	screw	screw
Body color	black	black
Body material	TPU	TPU
Coupling nut material	CuZn, Ni	CuZn, Ni
Contact carrier color	transparent	transparent
Contact carrier material	PA	PA
Contact plating	Au	Au
Contact material	CuSn (bronze)	CuSn (bronze)
Environmental data		
RoHS compliant	yes	yes
Ambient temperature (operation)	-30...+90°C, -22...+194°F	-30...+90°C, -22...+194°F
Protection rating	IP65/67/68 in screwed condition	IP65/67/68 in screwed condition
Pollution level	3	3
Approvals	UL listed, EAC	UL listed, EAC

Cable

Electrical data		
Rated voltage	100 V	
Insulation resistance	≥ 500 MΩ * km (DIN EN 50395)	
Unbalanced capacitance to ground	1600 pF/km	
Characteristic impedance	100 Ω ± 5 Ω	
Loop resistance	≤ 290 Ω/km	
Unbalanced resistance	< 3 %	
Dielectric strength wire/wire	700 V	
Dielectric strength wire/shield	700 V	
Signal running time	< 513 ns/100 m	
Electrical parameters (Ethernet)	Cat.7 acc. to EN50288-4-2	
Mechanical data		
Cable structure	S/FTP	
Cable structure (Ethernet)	twisted shielded pair	
Conductor construction (Ethernet)	7-strand	
Cross-section (Ethernet)	4 x 2 x 0.14 mm ² (AWG26)	

Outer cable diameter	6.4 mm ± 0.3mm (0.252" ± 0.0118")
Min. bending radius, moved	10 x outer cable diameter
Min. bending radius, fixed installation	5 x outer cable diameter
Weight	48 kg/km (32 lb/1000 ft)
Conductor material (Ethernet)	bare copper
Shielding	braiding of tinned copper wires, metallized plastic fleece for pair shielding
Optical covering factor of shielding (total)	≥ 70 %
Use	fixed installation
Jacket color	green
Material jacket	PUR (polyurethane)
Wire color code	white / blue, white / orange, white / green, white / brown
Wire insulation material	PE (polyethylene)
Printing on the jacket	"length in meters" LEONI L INDUSTRIAL ETHERNET FLEXIBLE PATCHCABLE PUR CAT7 PLUS *AWG26*RU AWM STYLE 20963 80 °C 30 V "year/ internal order number"

Environmental data


Operation temperature range, moved	-40...+80°C, -40...+176°F
Ambient temperature, transport/storage	-20...+60°C, -4...+140°F
UV resistance	good
Oil resistance	according to IEC 60811-2-1 or according to DIN VDE 0282 part 10
Acid, lye and solvent resistance	depends on medium, concentration, temperature and duration
Special features	Series of ISO/IEC 11801-x; Class F, Series of EN 50173-x; Class F, IEEE802.3: 10Base-T; 100Base-T; 1000Base-T; 10GBase-T, IEEE 802.3: Power over Ethernet PoE; PoE+
LABS-free	yes
Flame-retardant	according to IEC 60332-1-2 UL758 cable flame test
Halogen-free	according to IEC 60754-1
Silicone-free	yes
Approvals	UL file number: E130266, UL-Style AWM 20963

Attenuation


Max. insertion loss								
Frequency [MHz]	1	4	10	16	20	31.25	62.5	100
[db/100 m]	2.9	5.5	8.6	10.8	12.2	15.2	21.8	28.0
[db/100 ft]	0.9	1.7	2.6	3.3	3.7	4.6	6.6	8.5
Min. near-end crosstalk attenuation								
Frequency [MHz]	1	4	10	16	20	31.25	62.5	100
[db/100 m]	80	80.0	80.0	80.0	80.0	79.6	75.1	72.4

[db/100 ft]	24.4	24.4	24.4	24.4	24.4	24.3	22.9	22.1
-------------	------	------	------	------	------	------	------	------

Contact assembly



Dimensions



A1	50.5 mm
A2	Ø 15.0 mm
B1	50.5 mm
B2	Ø 15.0 mm

Notes

- Depending on the cable length (L), the following length tolerances apply:
0 m...<0.2 m: ± 10 mm | 0.2...4.0 m: + 40 mm | ≥ 4.0 m: + 1%
- Illustrations similar
- Further cable length on request.

CE, UL

CE	yes
----	-----

Ordering information

Ordering information	Length
ZK1096-8181-0003	0.30 m
ZK1096-8181-0004	0.40 m

ZK1096-8181-0005	0.50 m
ZK1096-8181-0006	0.60 m
ZK1096-8181-0010	1.00 m
ZK1096-8181-0015	1.50 m
ZK1096-8181-0020	2.00 m
ZK1096-8181-0030	3.00 m
ZK1096-8181-0050	5.00 m
ZK1096-8181-0075	7.50 m
ZK1096-8181-0100	10.00 m
ZK1096-8181-0150	15.00 m
ZK1096-8181-0200	20.00 m
ZK1096-8181-0250	25.00 m
ZK1096-8181-0300	30.00 m
ZK1096-8181-0400	40.00 m
ZK1096-8181-0500	50.00 m
ZK1096-8181-0850	85.00 m

Accessories

ZB8801-0000	torque wrench for hexagonal plugs, adjustable
ZB8801-0001	torque cable key, M8/wrench size 9, for ZB8801-0000
ZB8803-0001	Flange/Panel feed-through for M8 pre-assembled, for fixing the connector, plastic



Products marked with a crossed-out wheeled bin shall not be discarded with the normal waste stream. The device is considered as waste electrical and electronic equipment. The national regulations for the disposal of waste electrical and electronic equipment must be observed.

Beckhoff®, TwinCAT®, TwinCAT/BSD®, TC/BSD®, EtherCAT®, EtherCAT G®, EtherCAT G10®, EtherCAT P®, Safety over EtherCAT®, TwinSAFE®, XFC®, XTS® and XPlanar® are registered trademarks of and licensed by Beckhoff Automation GmbH. Other designations used in this publication may be trademarks whose use by third parties for their own purposes could violate the rights of the owners.

© Beckhoff Automation GmbH & Co. KG 02/2024

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual application do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.