



ZS7000-C012 | Crimp contact, M8 socket, female, AWG22/0.34 mm²

M8, female, turned

Mechanical data	
Accessories Type	crimp contact
Installation size	M8
Contact type	female, turned
Wire termination	crimp connection
Mating cycles	≥ 100
Contact plating	Ni, Au gal.
Contact material	copper alloy
Max. wire cross section	AWG22 (0.34 mm ²)
Contact diameter	0.8 mm

Notes

- Illustrations similar

Ordering information	
ZS7000-C012	Crimp contact, M8, socket, female, AWG22/0.34 mm ² , PU = 50 pieces

Accessories	
ZB8810-0000	crimping tool for Ethernet element, M8, B12, B17, B23 contacts
ZB8810-0001	crimping insert and locator for Ethernet element, M8, B12, B17 contacts

Beckhoff®, TwinCAT®, EtherCAT®, EtherCAT G®, EtherCAT G10®, EtherCAT P®, Safety over EtherCAT®, TwinSAFE®, XFC®, XTS® and XPlanar® are registered trademarks of and licensed by Beckhoff Automation GmbH. Other designations used in this publication may be trademarks whose use by third parties for their own purposes could violate the rights of the owners.

© Beckhoff Automation GmbH & Co. KG 02/2020

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual application do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.